

# Model | TSCI-1000R-G-PH~TSL01 RX3

Refrigerator Designed for Pharmacy/Vaccine Applications

## **Product Protection**

- Electronic temperature control with digital display.
- Temperature measured in a glycol-filled bottle displayed on the control to simulate actual product temperature.
- Audible and visual high/low temperature alarm.
- Door ajar alarm.
- Logs high and low cabinet temperature.
- Power Failure and Sensor Failure alarm.
- Control has a battery backup feature.
- Temperature Probe access port.

# R290 refrigerant

- Uses environmentally friendly R290 hydrocarbon refrigerant.
- Zero (0) ozone depletion potential (ODP).
- Zero (0) global warming potential (GWP).

# Self Cleaning Technology

Reverse Condensing
Fan Motor Technology
allows for the reversal of
the condensing fan motor,
helping to keep the
condensing coil clean
and reduce energy
consumption by as
much as 20%.

## **LED Lighting**

LED interior lighting provides more even lighting throughout the cabinet and is safety shielded.



with built-in antimicrobial properties to protect the handle.



## **Energy Efficiency**

Exceeds Energy Star Energy Requirements for Lab Grade Refrigeration by **72**%



## **High Capacity Refrigeration System**

- Meets CDC guidelines.
- High capacity, factory balanced refrigeration system that maintains cabinet temperatures of 2°C to 8°C (36°F to 46°F).
- True's air flow system is designed to promote air circulation throughout the entire cabinet.







AB\_245798\_03.25

## **Refrigeration System**

 State of the art, electronically commutated evaporator and condenser fan motors. ECM motors operate at higher peak efficiencies and move a more consistent volume of air which produces less heat, reduces energy consumption and provides greater motor reliability.

#### **Cabinet Construction**

- Exterior non-peel or chip white powder coated cold rolled steel; durable and permanent.
- **Interior** attractive white aluminum liner with stainless steel floor.
- Insulation entire cabinet structure is foamedin-place using a high density, polyurethane insulation that has zero ozone depletion potential (ODP) and zero global warming potential (GWP).
- Welded, heavy duty steel frame rail, white powder coated for corrosion protection.
- Frame rail fitted with leg levelers.

#### **Doors**

- "Low-E", double pane thermal insulated glass door assemblies with mitered plastic channel frames. The latest in energy efficient technology.
- Each door fitted with 12" (305 mm) long extruded handle. Advanced technology with built-in antimicrobial properties to protect the handle.
- Self closing doors. Positive seal, torsion type closure system.
- Magnetic door gaskets of one piece construction, removable without tools for ease of cleaning.

#### **Shelving**

- Fourteen (14) powder-coated, perforated sheet metal shelves 22 5% "D x 20 % "W (566 mm x 530 mm).
- Shelf support pilasters made of same material as cabinet interior; shelves are adjustable in  $V_2$ " (13 mm) increments.

### **Electrical**


• Unit completely pre-wired at factory and ready for final connection to a 115/60/1 phase, 15 amp dedicated outlet. Cord and plug set included.



#### **Options**

- Additional shelves
- External Alarm Relay
- · Stainless steel exterior and interior
- Castors
- 2 inch access ports (2P)
- Internal duplex outlet (1D)
- 2.5 inch castors
- Wire shelves
- Chromatography mast

## PLAN VIEW DRAWINGS



			Cabinet Dimensions (inches) (mm)						NEMA	Cord Length	Crated Weight
Model	Doors	Shelves	W	D†	Н	HP	Voltage	Amps	Config.	(total ft) (total m)	(lbs) (kg)
TSCI-1000R-G-PH~TSL01RX3	2	14	471/8	29%	785/8	1/4	115/60/1	2.8	5-15P	9	495
			1197	759	1997	N/A		N/A		2.74	224.5

Unifo (°	mp ormity C) F)	Temp Stability (°C) (°F)	Energy Usage (kWh)	Daily Rejected Heat (BTU/hr)	Temp Range (min) (max)	Energy Star Certified	Internal Volume (cu. ft.) (Liters)	Probe Port(s) / Diameter (in.)	Temp. Set Point (°C) (°F)
0	.8	0.7	2.403	762	2°C	Yes	38.2	1	5
					8°C		1082	0.625	41

† Depth does not include 1½" (37 mm) for door handle or 5%" for rear mechanical components.